
Typical application



Mounting the Indicator Holder



Standard Accessories

• 513-401-10H (Metric)

- 902053: Clamp 601471: Indicator holder
- 538616: Hexagonal-head wrench (3 mm)
- Note: Inspection certificate is not attached. Contact your local Mitutoyo sales office.

Optional Accessories

- 900565: Feeler
- 900571: Adjustable holder
- 900551: Extension holder

Square Master SERIES 311 — Squareness/Straightness Measuring

- Squareness (perpendicularity) and straightness Sliding force: Approx. 2 to 5 N measurements can be performed accurately and efficiently by just moving a lever. Use the vertical motion handle on the rear of the main unit for operation.
- Highly accurate measurement of squareness and straightness is available by calibrating a square as a master using the built-in perpendicularity adjustment mechanism. Prepare a square to be used for accuracy check/adjustment separately.





SPECIFICATIONS Motric


| Order No. | Vertical travel (mm) | Squareness (µm) | Straightness (µm) | Dir Width | nension (m Depth | nm) Height | Mass (kg) |
|-----------|-------------------------|--------------------|----------------------|--------------|---------------------|---------------|--------------|
| 311-215* | 150 | 3 | 2 | 180 | 200 | 420 | 13.7 |
| 311-225* | 250 | 6 | 2.5 | 180 | 200 | 520 | 16.2 |
| 311-245 | 450 | 9 | 3.5 | 220 | 220 | 720 | 24 |
| - | | | | | | | |

* Riser blocks to extend the height of Square Masters can be used. (Refer to Page E-36 for details)

Optional accessories


900565: Feeler

For probing surfaces that the contact point of a detector cannot reach.




900571: Adjustable holder

Enables easy adjustment of indicator position.



Unit: mm



900551: Extension holder

Measurement position can be extended by using this 200 mm length holder instead of the indicator holder.

